



More information on the website  
[mirror.radwag.com/us/info,w1,92V](https://mirror.radwag.com/us/info,w1,92V)

# MA 50/1.5Y.WH Moisture Analyzer

WL-304-0048



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Autotest



Statistics



IR sensors



GLP Procedures



Replaceable unit



Statistical Quality Control



ALIBI Memory



Drying modes



Samples drying



Moisture content  
analysis



Dry mass determination



Wi-Fi

## Datasheet

| Maximum capacity [Max]         | 50 g                                            |
|--------------------------------|-------------------------------------------------|
| Readability [d]                | 0,1 mg                                          |
| Tare range                     | -50 g                                           |
| Adjustment                     | external                                        |
| Maximum sample weight          | 50 g                                            |
| Heating module                 | halogen                                         |
| Moisture content repeatability | ±0,05 % (sample ~ 2 g), ±0,01 % (sample ~ 10 g) |
| Moisture content readability   | 0,0001 %                                        |

|                                     |                                                                                                                                    |
|-------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Drying temperature range            | Max 250 °C                                                                                                                         |
| <b>Physical parameters</b>          |                                                                                                                                    |
| Leveling system                     | semi-automatic – LevelSENSING                                                                                                      |
| Display                             | 10" graphic colour touchscreen                                                                                                     |
| Weighing chamber                    | automatic                                                                                                                          |
| Delivery components                 | Moisture Analyzer, disposable pan x 10, cross-shaped holder, drying pan handle, weighing pan shield, fabric dust cover, power cord |
| Maximum sample height               | 20 mm                                                                                                                              |
| Weighing pan dimensions             | ø90, h= 8 mm                                                                                                                       |
| Packaging dimensions W x D x H      | 540×610×470 mm                                                                                                                     |
| Net weight                          | 5,3 kg                                                                                                                             |
| Gross weight                        | 13 kg                                                                                                                              |
| <b>Construction</b>                 |                                                                                                                                    |
| Protection class                    | IP 43                                                                                                                              |
| <b>Features of use</b>              |                                                                                                                                    |
| Display mode                        | %D, %M, %R, g                                                                                                                      |
| Drying method                       | 4 drying profiles (standard, fast, step, mild)                                                                                     |
| Finish mode                         | 4 modes (automatic, manual, time-defined, user-defined)                                                                            |
| Additional functions                | sample traceability                                                                                                                |
| Communication interface             | 2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot                                                                      |
| Power supply                        | 100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz                                                                                   |
| Power consumption                   | 6 W                                                                                                                                |
| Heating module power                | 450 W                                                                                                                              |
| Operating temperature               | +10 – +40 °C                                                                                                                       |
| Mass indication control             | External mass standard 50g, 100g, 200g, depending on the type of moisture analyzer (additional equipment)                          |
| Drying temperature adjustment       | Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)        |
| Drying temperature control          | One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)                         |
| Moisture content indication control | Certified MV Test Set (additional equipment)                                                                                       |

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Antivibration tables  
Moisture analyzer accessories  
Additional modules  
Barcode scanners  
Receipt Printer

Fingerprint Reader  
RS 232, RS 485 cables  
RS 232 cables (scale - printer)  
RS 232 – RS 485 Converter

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

## Device dimensions W x D x H

