



More information on the website  
[mirror.radwag.com/en/info,w1,9LN](http://mirror.radwag.com/en/info,w1,9LN)

# PLC/4/600/C6 Platform

WX-009-0023



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                                |
|--------------------------|--------------------------------|
| Maximum capacity [Max]   | 600 kg                         |
| Readability [d]          | 200 g                          |
| Construction             |                                |
| Protection class         | IP 65 construction, IP 67 cell |
| Construction             | mild steel St3S                |
| Weighing pan material    | mild steel St3S                |
| Physical parameters      |                                |
| Weighing pan dimensions  | 800x800 mm                     |
| Weighing platform height | 120 ± 10 mm                    |

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.



## Accessories (Additional Fee)

CY10 Scales for PGC  
PUE CY10 Weighing Terminal  
CY10 Multifunctional Scale  
PUE 5 Weighing Terminal  
CY10 Precision Balance  
PUE HX7 Weighing Terminal

PUE C32 Weighing Terminal  
PUE 7.1 Weighing Terminal  
Frame for embedded scales  
PUE C315 Weighing Terminal  
PUE HY10 Weighing Terminal  
PUE H315 Weighing Terminal

# Device dimensions W x D x H



| Platform   | A    | B    | H       |
|------------|------|------|---------|
| PLC/4/C6   | 800  | 800  | 120 ±10 |
| PLC/4/C7   | 1000 | 1000 | 120 ±10 |
| PLC/4/C8   | 1200 | 1200 | 120 ±10 |
| PLC/4/C8/9 | 1200 | 1500 | 120 ±10 |
| PLC/4/C9   | 1500 | 1500 | 120 ±10 |
| PLC/4/C10  | 1500 | 2000 | 120 ±10 |
| PLC/4/C11  | 2000 | 2000 | 120 ±10 |

dimensions in mm

## PLC/4/C



PL/4/H6/Z  
PL/4/H7/Z  
PL/4/H8/Z



PL/4/H8/9/Z  
PL/4/H9/Z  
PL/4/H10/Z



| Platform  | A    | B    | H      |
|-----------|------|------|--------|
| PL/4/H6   | 800  | 800  | 88 ±2  |
| PL/4/H7   | 1000 | 1000 | 88 ±2  |
| PL/4/H8   | 1200 | 1200 | 88 ±2  |
| PL/4/H8/9 | 1200 | 1500 | 88 ±2  |
| PL/4/H9   | 1500 | 1500 | 88 ±2  |
| PL/4/H10  | 1500 | 2000 | 111 ±2 |

dimensions in mm

## PL/4/H



| Platform    | A    | B    | H      |
|-------------|------|------|--------|
| PL/4/H6/Z   | 800  | 800  | 88 ±2  |
| PL/4/H7/Z   | 1000 | 1000 | 88 ±2  |
| PL/4/H8/Z   | 1200 | 1200 | 88 ±2  |
| PL/4/H8/9/Z | 1200 | 1500 | 88 ±2  |
| PL/4/H9/Z   | 1500 | 1500 | 88 ±2  |
| PL/4/H10/Z  | 1500 | 2000 | 111 ±2 |

dimensions in mm

## PL/4/H/Z