



More information on the website  
[mirror.radwag.com/us/info,w1,9N8](http://mirror.radwag.com/us/info,w1,9N8)

# MWMH 100-1 Electromagnetic Compensation Weighing Module

WX-016-0061



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

### Metrological parameters

Maximum capacity [Max]	1 kg
Minimum load	2 g
Preload range	6 – 9 kg
Readability [d]	0,01 g
Verification unit [e]	0,1 g
Tare range	-1 kg
Repeatability	0,01 g
Stabilization time	0,1 s
Adjustment	external
OIML Class	III
Sensitivity temperature drift	$2 \times 10^{-6} / ^\circ\text{C} \times \text{Rt}$

### Construction

Protection class	IP 65
Material	Stainless steel

Communication interface	
Communication interface	RS232, Ethernet, 2×IN / 2×OUT
Electrical parameters	
Power supply	12 – 24 V DC
Power consumption max.	5 W
Environmental conditions	
Operating temperature	+10 – +40 °C
Storage temperature	-20 – +50 °C
Relative humidity	15% – 80%
Physical parameters	
Weighing pan dimensions	212×174 mm
Device dimensions W x D x H	344×224×166 mm
Packaging dimensions W x D x H	580×413×360 mm
Net weight	12,4 kg
Gross weight	15 kg




## Accessories (Additional Fee)

RS 232 – USB Converter

## Software (Additional Fee)

- MWMH Manager [WX-010-0103]
- Scale Editor - EWAG 2.1 [WX-010-0173]
- RAD Key [WX-010-0005]
- RADWAG Development Studio [WX-010-0104]

# Device dimensions W x D x H



MWMH IP 69K