



More information on the website
mirror.radwag.com/us/info,w1,A0E

High Resolution Platforms

PL.600.HRP.EX.H

WX-009-0287



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|--------------------------------|----------------------|
| Maximum capacity [Max] | 600 kg |
| Preload range | 60 kg |
| Readability [d] | 5 g |
| Tare range | -600 kg |
| Repeatability | 7,5 g |
| Linearity | ±15 g |
| Adjustment | internal (automatic) |
| Physical parameters | |
| Cable length | 10 m |
| Weighing pan dimensions | 1000×800 mm |
| Packaging dimensions W x D x H | 1200×1000×436 mm |
| Net weight | 126 kg |
| Gross weight | 160 kg |

| Construction | |
|-------------------------|--|
| Protection class | IP 66 / 67 |
| ATEX Certification | II 3G Ex ic IIC T4 Gc II 3D Ex ic IIIC T60°C Dc |
| IECEx Certification | Ex ic IIC T4 Gc Ex ic IIIC T60°C Dc |
| Construction | Stainless steel AISI304 |
| Weighing pan material | Stainless steel AISI304 |
| | |
| Communication interface | RS485 |
| | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| | |
| Operating temperature | +10 – +40 °C |
| Relative humidity | 15% – 80% |



Accessories (Additional Fee)

PUE HX5.EX Weighing Terminal
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX Weighing Terminal



Receipt Printer

Software (Additional Fee)



- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

Device dimensions W x D x H



PL.16 - 32.HRP.H



PL.62-2000.HRP.H

| Scale type | A1 | A2 | H |
|-----------------------|------|------|-------|
| PL.(16-32).HRP.H | 360 | 280 | 180±5 |
| PL.(62-150).HRP.H | 500 | 400 | 180±5 |
| PL.150.2.HRP.H | 500 | 500 | 180±5 |
| PL.(150.1-300).HRP.H | 800 | 600 | 180±5 |
| PL.(300.1-1100).HRP.H | 1000 | 800 | 180±5 |
| PL.(2000).HRP.H | 1250 | 1000 | 180±5 |

Dimensions in mm