



More information on the website
mirror.radwag.com/tr/info,w1,A2E

HX5.EX-1.60.HR4 Tek Yük Hücreli Platform Terazi

WW-007-0012



The drawings, photos and graphics used are for illustrative purposes only.

Fonksiyonlar



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Teknik Veriler

| Metrolojik parametreler | |
|--------------------------|--------|
| Maksimum yük [Max] | 60 kg |
| Minimum yük [Min] | 400 g |
| Okuma için ruluęu [d] | 20 g |
| Yasallařtırma birimi [e] | 20 g |
| Dara aralıęı | -60 kg |
| OIML sınıfı | III |

| Fiziksel parametreler | |
|-----------------------------|---|
| Display | 5" grafik renkli |
| Kablo uzunluđu | 2,5 m |
| Tartım kefesi boyutları | 500x500 mm |
| Ambalaj boyutları G x D x Y | 610x640x550 mm |
| Net ađırlık | 24,8 kg |
| Brüt ađırlık | 28,5 kg |
| Konstrüksiyon | |
| IP Sınıfı | IP 66 / 67 / 69 konstrüksiyon, IP 66 / 68 terminal |
| Sertifikasyon ATEX | II 2G Ex ib IIC T4 Gb II 2D Ex ib IIIC T135°C Db |
| Sertifikasyon IECEx | Ex ib IIC T4 Gb Ex ib IIIC T135°C Db |
| Konstrüksiyon | Paslanmaz elik AISI316 |
| Tartım kefesi | Paslanmaz elik AISI316 |
| Haberleşme arayüzler | |
| Haberleşme arayüzü | 2xRS232, RS485 |
| Elektrik parametreleri | |
| Güç kaynađı | 100 – 240 V AC 50/60 Hz |
| Maksimum güç tüketimi | 15 W |
| Çevresel koşullar | |
| Çalıştırma sıcaklığı | -10 – +40 °C |
| Atmosferik nem | 10% – 85% RH yoğunlaşma yok |
| İndikatör | PUE HX5.EX-1 |



Additional fee for verification



Aksesuarlar (Additional Fee)

Haberleşme modülü
Terazi için tasarlanmış kendinden korumalı güç kaynađı

Fiş yazıcı

Yazılım (Additional Fee)

- E2R Tartım [WX-010-0099]
- Etiket Editörü R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Alibi Okuyucu PC Yazılımı [WX-010-0114]
- Terazi Editörü - EWAG 2.1 [WX-010-0173]

Cihaz boyutları G x D x Y

| Scale type | A1 | A2 | B |
|----------------|-----|-----|-------|
| HX5.EX-1.HR2 | 250 | 300 | 103±3 |
| HX5.EX-1.HR3 | 410 | 410 | 98±2 |
| HX5.EX-1.HR4 | 500 | 500 | 155±5 |
| HX5.EX-1.HR3/5 | 400 | 600 | 155±5 |
| HX5.EX-1.HR5 | 600 | 600 | 155±5 |

Dimensions in mm



PUE HX5.EX-1



Platform H