



More information on the website  
[mirror.radwag.com/us/info,w1,A6P](http://mirror.radwag.com/us/info,w1,A6P)

# CY10.60/120.C2.K Precision Balance

WL-225-1008



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	60 / 120 kg
Minimum load	-
Readability [d]	1 / 2 g
Verification unit [e]	-
Tare range	-120 kg
Repeatability	2 g
Linearity	±2 g

<b>Metrological parameters</b>	
Stabilization time	3 s
Adjustment	external
OIML Class	-
<b>Physical parameters</b>	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	2,5 m
Weighing pan dimensions	400×500 mm
Packaging dimensions W x D x H	720×620×210 mm
Net weight	13,5 kg
Gross weight	16 kg
<b>Construction</b>	
Protection class	IP 43
Housing	steel + ABS
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
<b>Electrical parameters</b>	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10–19W*
<b>Environmental conditions</b>	
Operating temperature	+15 – +30 °C
Storage temperature	-25 – +70 °C
Relative humidity	10% – 80% RH no condensation

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

MediaBox  
Mild steel powder coated weighing platforms  
RFID Tags  
Antivibration tables  
Power Adapters  
Additional Weighing platforms Module  
Additional modules  
Platforms in plastic casing  
Professional Weighing Tables

Protective cover for balances  
Barcode scanners  
RS 232, RS 485 cables  
Label Printers  
Stands, wall mounting kits and mounting brackets  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions W x D x H

