



More information on the website
mirror.radwag.com/en/info,w1,A71

PLC/150/C2 Platform

WX-009-0005



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|-------------------------|-------------------------|
| Maximum capacity [Max] | 150 kg |
| Readability [d] | 50 g |
| Construction | |
| Protection class | IP 65 |
| Construction | mild steel St3S |
| Weighing pan material | Stainless steel AISI304 |
| Physical parameters | |
| Weighing pan dimensions | 400×500 mm |
| Packaging dimensions | 720×620×210 mm |

Readability accuracy – expected value, dependent on the parameters of the measuring transmitter used.



Accessories (Additional Fee)

CY10 Scales for PGC
 PUE CY10 Weighing Terminal
 CY10 Multifunctional Scale
 PUE 5 Weighing Terminal
 CY10 Precision Balance
 PUE C32 Weighing Terminal

PUE 7.1 Weighing Terminal
 PUE HX7 Weighing Terminal
 PUE C315 Weighing Terminal
 PUE HY10 Weighing Terminal
 PUE H315 Weighing Terminal


Device dimensions



PL/D2




PLC/F1



PLC/C2
PLC/C3



PL/H
PL/HR



| Platform type | A1 | A2 | H |
|---------------------|-----|-----|-------|
| PL/D2 | 238 | 216 | 82±3 |
| PLC/F1 | 300 | 300 | 70±3 |
| PLC/C2 | 402 | 502 | 103±3 |
| PLC/C3 | 701 | 501 | 130±5 |
| PL/H1 / PL/HR1 | 150 | 200 | 85±3 |
| PL/H2 / PL/HR2 | 250 | 300 | 103±3 |
| PL/H3 / PL/HR/3 | 410 | 410 | 98±3 |
| PL/H3/5 / PL/HR/3/5 | 400 | 600 | 155±3 |
| PL/H4 / PL/HR/4 | 500 | 500 | 155±3 |
| PL/H5 / PL/HR/5 | 600 | 600 | 155±3 |
| PL/H6 | 800 | 800 | 135±3 |

dimensions in mm