



More information on the website
mirror.radwag.com/en/info,w1,A8R

HX5.EX-1.4N.600.H4 Stainless Steel Ramp Scale

WW-009-0038



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit
measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	600 kg
Minimum load	4 kg
Readability [d]	200 g
Verification unit [e]	200 g
Tare range	-600 kg
OIML Class	III

Physical parameters		
Display		5" graphic colour
Cable length		3 m
Weighing pan dimensions		1500×1500 mm
Device dimensions W x D x H		2450×1820×77 mm
Construction		
Protection class		IP 66 / 69 construction, IP 66 / 68 terminal
ATEX Certification		II 2G Ex ib IIC T4 Gb II 2D Ex ib IIIC T135°C Db
IECEX Certification		Ex ib IIC T4 Gb Ex ib IIIC T135°C Db
Construction		Stainless steel AISI304
Communication interface		
Communication interface		2×RS232, RS485
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz
Power consumption max.		15 W
Environmental conditions		
Operating temperature		-10 – +40 °C
Relative humidity		10% – 85% RH no condensation
Indicator		PUE HX5.EX-1



Additional fee for verification



Accessories (Additional Fee)

Communication Modules
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
Weighing Terminal

Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]