



More information on the website
mirror.radwag.com/us/info,w1,ARS

SM-MYA 5.5Y Susceptometer

WL-101-1084



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
E1 Calibration Range	2 g – 50 kg
E2 Calibration Range	2 g – 50 kg
F1 Calibration Range	2 g – 50 kg
F2 Calibration Range	2 g – 50 kg
Maximum capacity [Max]	50 kg
Readability [d]	1 µg
Standard repeatability [Max]	1,6 µg
Standard repeatability [5% Max]	0,6 µg
Linearity	±3 µg
Stabilization time	10 s
Adjustment	internal (automatic)
Calibration Range	2 g – 50 kg
Distance platform Z0	18; 20; 27; 35; 43 mm
Magnetizing field strenght	2700, 2000, 800, 380, 200 A/m

Physical parameters	
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Weighing pan dimensions	ø300 mm
Device dimensions W x D x H	525×350×250 mm
Packaging dimensions W x D x H	950×750×750 mm
Net weight	26 kg
Gross weight	36 kg
Dipole moment of magnets	≤ 0,1 Am ²
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Environmental conditions	
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0,5 °C / 12 h (±0,3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±2% / 4 h
Construction	
Housing	ABS plastic
Components and software	
Processor	2×1 GHz
Memory	RAM 256 MB DDR2, 16GB – microSD

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

RFID Tags
 Antivibration tables
 Additional modules
 Protective cover for balances

THBR 2.0 System - Ambient Conditions Monitoring
 RS 232, RS 485 cables
 Receipt Printer
 Fingerprint Reader

Software (Additional Fee)

• RMCS System Network Management of Calibration Process [WX-010-0048]