



More information on the website  
[mirror.radwag.com/en/info,w1,ASO](http://mirror.radwag.com/en/info,w1,ASO)

# C32.20.PM Precision Balance

WL-223-0079



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Labelling
-  Plus/Minus Control
-  Percent Weighing
-  Totalizing
-  Parts counting
-  Newton unit measurement
-  Statistics
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Density determination
-  Replaceable unit
-  ALIBI Memory

## Datasheet

Metrological parameters	
Maximum capacity [Max]	20 kg
Minimum load	-
Preload range	2 kg
Readability [d]	0.01 g
Tare range	-20 kg
Minimum weight (USP)	8.2 g

Metrological parameters	
Minimum weight (U=1%, k=2)	0.82 g
Repeatability (Max)	0.02 g
Repeatability (5% Max)	0.0041 g
Linearity	±0.03 g
Stabilization time	1.5 s
Adjustment	internal (automatic)
OIML Class	-
Physical parameters	
Leveling system	manual
Display	5" graphic colour
Weighing pan dimensions	200×185 mm
Packaging dimensions W x D x H	520×520×280 mm
Net weight	11.3 kg
Gross weight	13 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	100 - 240 V AC 50 / 60 Hz
Power consumption max.	0.5 A
Environmental conditions	
Operating temperature	+10 – +40 °C

**Repeatability** is expressed as a standard deviation from 10 weighing cycles.

**Stabilization time** depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

**Preload** - value equal to ±10% of the maximum load [Max] of the legalised balance. It is possible to start the balance with the mass placed on the pan equal to the maximum preload value.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Displays  
 Antivibration Tables  
 Power Adapters  
 RS 232 cables (scale - printer)  
 Cigarette lighter receptacle power supply cables  
 Professional Weighing Tables

Barcode scanners  
 Under-pan weighing  
 RS 232, RS 485 cables  
 Stands, wall mounting kits and mounting brackets  
 Receipt Printer  
 AP2-1 Current Loop Unit

## Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• RAD Key [WX-010-0005]

- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

## Device dimensions W x D x H

