



More information on the website
mirror.radwag.com/en/info,w1,AVS























PS 4500.X7.M.PGC Precision Balance

WK-313-0003



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Plus/Minus Control
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Density determination
-  Ambient conditions monitoring
-  Replaceable unit
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Mass for titrator
-  Wi-Fi

Datasheet

Metrological parameters

| | |
|------------------------|--------|
| Maximum capacity [Max] | 4500 g |
| Minimum load | 5 g |

| Metrological parameters | |
|---------------------------------|--|
| Readability [d] | 0.1 g |
| Verification unit [e] | 0.1 g |
| Tare range | -4500 g |
| Minimum weight (USP) | 10 g |
| Minimum weight (U=1%, k=2) | 1 g |
| Repeatability (Max) | 0.008 g |
| Repeatability (5% Max) | 0.005 g |
| Linearity | ±0.02 g |
| Stabilization time | 1.5 s |
| Adjustment | internal (automatic) |
| OIML Class | II |
| Sensitivity temperature drift | $2 \times 10^{-6} / ^\circ\text{C} \times \text{Rt}$ |
| Physical parameters | |
| Leveling system | manual |
| Display | 7" graphic colour touchscreen |
| Delivery components | Balance, weighing pan, weighing pan shield, power supply |
| Weighing pan dimensions | 195×195 mm |
| Device dimensions W x D x H | 333x206x107 mm |
| Packaging dimensions W x D x H | 476×381×346 mm |
| Net weight | 4.64 kg |
| Gross weight | 6.04 kg |
| Construction | |
| Protection class | IP 43 |
| Features of use | |
| Touch-free operation | 2 IR Sensors |
| Communication interface | |
| Communication interface | 2×RS232 ¹ , USB-A, USB-B, Ethernet, Wi-Fi |
| Electrical parameters | |
| Power supply | Adapter: 100 – 240V AC 50/60Hz 0.6A Max; 12V DC 1.2A Balance: 12 – 15V DC 0.9A max; 4 – 8W* |
| Power consumption | 4 W |
| Environmental conditions | |
| Operating temperature | +10 – +40 °C |
| Storage temperature | -20 – +50 °C |
| Relative humidity | 40% – 80% |

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

Balance Storage Case
Power Adapters
Cigarette lighter receptacle power supply cables
USB cable (scale - printer)
Barcode scanners
Antivibration Tables
Displays
Density determination KIT

Protective cover for balances
Receipt Printer
RS 232, RS 485 cables
Additional modules
Under-pan weighing
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter

Software (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

- E2R PGC [WX-010-0051]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]