



More information on the website
mirror.radwag.com/en/info,w1,AXX

CY10.3/6.F1.K.M2.PGC Scale

WK-312-1003



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Packaged Goods Control



Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	3 / 6 kg
Minimum load	25 / 50 g
Readability [d]	0.5 / 1 g
Verification unit [e]	0.5 / 1 g
Tare range	-6 kg
Stabilization time	3 s
Adjustment	external

Metrological parameters	
OIML Class	II
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	1 m
Weighing pan dimensions	300×300 mm
Packaging dimensions W x D x H	570×390×170 mm
Net weight	6.2 kg
Gross weight	7 kg
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max; 10–19W*
Environmental conditions	
Operating temperature	+15 – +30 °C
Storage temperature	-25 – +70 °C
Relative humidity	10% – 80% RH no condensation

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

MediaBox
Mild steel powder coated weighing platforms
HRP Platforms High Capacity
RFID Tags
Power Adapters
Additional Weighing platforms Module

Platforms in plastic casing
Protective cover for balances
Label Printers
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions W x D x H

