



More information on the website
mirror.radwag.com/en/info,w1,AZ4

PUE C32 Weighing Terminal

WX-008-0141



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Physical parameters	
Display	5" graphic colour
Device dimensions	206×140×71 mm
Packaging dimensions	300×250×130 mm
Net weight	0.7 kg
Gross weight	0.94 kg
Construction	
Protection class	IP 43

Construction	
Housing	ABS plastic
Communication interface	
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Optional power supply	internal rechargeable battery
Operation time on batteries	operation time up to 5 h
Metrological parameters	
Maximum quantity of verification units	6000 e
Minimum voltage per verification unit	0.4 µV
Maximum voltage per verification unit	3.25 µV
Minimum load cell impedance	50 Ω
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V DC
Maximum increase of signal	39 mV
Connection of load cells	4 or 6 wires + shield
Environmental conditions	
Operating temperature	-10 – +40 °C
Multiple range	YES
Features of use	
Max number of platforms	1

* - optional version

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Compatible with (Additional Fee)

Mild steel powder coated weighing platforms
 Displays
 RS 232 cables (scale - ZEBRA printer)
 Power Adapters
 RS 232 cables (scale - printer)
 Mild steel powder coated weighing platforms
 Platforms in plastic casing
 USB cable (scale - printer)
 Barcode scanners

RS 232, RS 485 cables
 Label Printers
 Displays
 Keypad, external switches
 Stands, wall mounting kits and mounting brackets
 Additional modules
 Receipt Printer
 RS 232, RS 485 cables

Software (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- E2R Weighing Records [WX-010-0038]

Device dimensions

