



More information on the website
mirror.radwag.com/us/info,w1,B1G


PUE 7.1 Weighing Terminal

WX-008-0025



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



Animal weighing



Differential weighing



ALIBI Memory

Datasheet

OIML Class	III
Maximum quantity of verification units	6000 e
Minimum voltage per verification unit	0,4 μ V
Maximum voltage per verification unit	3,25 μ V
Minimum load cell impedance	50 Ω
Maximum load cell impedance	1200 Ω

Load cell excitation voltage	5V DC
Maximum increase of signal	19,5 mV
Physical parameters	
Display	5,7" Resistive Color Touchscreen
Device dimensions W x D x H	206x140x71 mm
Packaging dimensions W x D x H	300x250x130 mm
Net weight	0,6 kg
Gross weight	1,2 kg
Construction	
Protection class	IP 43
Keypad	touch screen
Housing	ABS plastic
Software	
Database capacity	16 GB (micro SD)
Operating system	Linux
Processor	quad-core 64-bit Cortex-A53 1,2 GHz
Memory	RAM 1GB LPDDR2
Data memory	16 GB (micro SD)
Connectivity	
Communication interface	2xRS232, 2xUSB-A, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Additional DP6 A/C converter module	1 (option)
Power	
Power consumption max.	max. 1 A
Environmental	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation
Number of buttons	8
Features of use	
Max number of platforms	2

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Compatible with (Additional Fee)

Waterproof stainless steel platforms
Mild steel powder coated weighing platforms
Displays
HRP Platforms High Capacity
Stainless steel HRP.H platforms
Power Adapters
Stainless steel platforms, pit version
RS 232 cables (scale - printer)
Ramp stainless steel platforms

Barcode scanners
Stainless steel ramp platforms with LD lifting system
RS 232, RS 485 cables
Label Printers
IN/OUT Cables
Keypad, external switches
Stands, wall mounting kits and mounting brackets
Receipt Printer
AP2-1 Current Loop Unit

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Audit Trail Reader [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions W x D x H

