




More information on the website
mirror.radwag.com/en/info,w1,B6L

DWT/RC HPW Checkweigher

WK-106-004_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	15 – 60 kg
Readability [d]	5 – 20 g
Verification unit [e]	5 – 20 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	mild steel / Stainless steel
Communication interface	
Communication interface	RS232, USB, Ethernet, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions	
Operating temperature	+5 – +40 °C
Components and software	
Operating system	Microsoft Windows 11 IoT
Features of use	
Capacity	max 100 pcs/min
Conveyor velocity	1.7 m/s

*OIML class for checkweighers used in packaged goods control (PGC) systems.



Accessories (Additional Fee)

Displays

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]