



More information on the website  
[mirror.radwag.com/en/info,w1,B85](http://mirror.radwag.com/en/info,w1,B85)

# TMX15C.150.H6.K Multifunctional Scale

WP-119-0047



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Labelling



Plus/Minus Control



Parts counting



Formulation



Statistics



Checkweighing

## Datasheet

### Metrological parameters

Maximum capacity [Max]	150 kg
Minimum load	1 kg
Readability [d]	50 g
Verification unit [e]	50 g
Tare range	-150 kg
Max readability for non-verified scale	10 g
OIML Class	III

### Physical parameters

Display	15.6" graphic colour touchscreen
---------	----------------------------------

<b>Physical parameters</b>	
Cable length	2.5 m
Weighing pan dimensions	800×800 mm
Controlling device dimensions	560×360×240 mm
Packaging dimensions W x D x H	820×1250×510 mm
<b>Construction</b>	
Protection class	IP 66 / 67 construction, IP 66 / 67 / 69 terminal
<b>Communication interface</b>	
Communication interface	4×USB 2.0 (2×USB-A, 2×M12 4P), Ethernet - 2×10/100/1000 Mbit (2×RJ45 hermetic), Profibus DP (operation mode: slave), 2×RS232, RS485 (2×M12 8P), 4IN / 4OUT (2×ports M12 8P or 2×cables fed through the cable gland)
Optional interfaces	external buttons PRINT, TARE, START - terminal with 4IN/4OUT (M12 8P connector) is required, additional weighing platform module - max. 3 pcs, metrological parameters as in the main weighing platform
<b>Electrical parameters</b>	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption	45 W
<b>Environmental conditions</b>	
Operating temperature	0 – +40 °C
Relative humidity	10% – 85% RH no condensation
<b>Components and software</b>	
Operating system	Microsoft Windows 11 IoT



Additional fee for verification



## Accessories (Additional Fee)

RS 232 cables (scale - printer)  
 Transponder card readers  
 RS 232 cables (scale - ZEBRA printer)  
 Ethernet cables (scale - Ethernet)  
 Displays  
 RS 232, RS 485 cables  
 Barcode scanners

Label Printers  
 Additional Weighing platforms Module  
 USB adapter  
 Receipt Printer  
 F1 Mass Standard -  
 knob weights without adjustment chamber, set  
 USB cable (scale - printer)  
 RS 232 – USB Converter

## Software (Additional Fee)

• RAD Key [WX-010-0005]  
 • R-Lab [WX-010-0080]

• Label Editor R02 [WX-010-0094]