



More information on the website  
[mirror.radwag.com/en/info,w1,BGI](http://mirror.radwag.com/en/info,w1,BGI)

# PLC/4/6000/C11 Platform

WX-009-0033



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                                |
|--------------------------|--------------------------------|
| Maximum capacity [Max]   | 6000 kg                        |
| Readability [d]          | 2 kg                           |
| Construction             |                                |
| Protection class         | IP 65 construction, IP 67 cell |
| Construction             | mild steel St3S                |
| Weighing pan material    | mild steel St3S                |
| Physical parameters      |                                |
| Weighing pan dimensions  | 2000×2000 mm                   |
| Weighing platform height | 160 ± 10 mm                    |

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.



## Accessories (Additional Fee)

CY10 Scales for PGC  
PUE CY10 Weighing Terminal  
CY10 Multifunctional Scale  
PUE 5 Weighing Terminal  
CY10 Precision Balance  
PUE C32 Weighing Terminal

PUE 7.1 Weighing Terminal  
PUE HX7 Weighing Terminal  
PUE C315 Weighing Terminal  
PUE HY10 Weighing Terminal  
PUE H315 Weighing Terminal

## Device dimensions



| Platform   | A    | B    | H       |
|------------|------|------|---------|
| PLC/4/C6   | 800  | 800  | 120 ±10 |
| PLC/4/C7   | 1000 | 1000 | 120 ±10 |
| PLC/4/C8   | 1200 | 1200 | 120 ±10 |
| PLC/4/C8/9 | 1200 | 1500 | 120 ±10 |
| PLC/4/C9   | 1500 | 1500 | 120 ±10 |
| PLC/4/C10  | 1500 | 2000 | 120 ±10 |
| PLC/4/C11  | 2000 | 2000 | 120 ±10 |

dimensions in mm

PLC/4/C



PL/4/H6/Z  
 PL/4/H7/Z  
 PL/4/H8/Z



PL/4/H8/9/Z  
 PL/4/H9/Z  
 PL/4/H10/Z



| Platform  | A    | B    | H      |
|-----------|------|------|--------|
| PL/4/H6   | 800  | 800  | 88 ±2  |
| PL/4/H7   | 1000 | 1000 | 88 ±2  |
| PL/4/H8   | 1200 | 1200 | 88 ±2  |
| PL/4/H8/9 | 1200 | 1500 | 88 ±2  |
| PL/4/H9   | 1500 | 1500 | 88 ±2  |
| PL/4/H10  | 1500 | 2000 | 111 ±2 |

dimensions in mm

PL/4/H



| Platform    | A    | B    | H      |
|-------------|------|------|--------|
| PL/4/H6/Z   | 800  | 800  | 88 ±2  |
| PL/4/H7/Z   | 1000 | 1000 | 88 ±2  |
| PL/4/H8/Z   | 1200 | 1200 | 88 ±2  |
| PL/4/H8/9/Z | 1200 | 1500 | 88 ±2  |
| PL/4/H9/Z   | 1500 | 1500 | 88 ±2  |
| PL/4/H10/Z  | 1500 | 2000 | 111 ±2 |

dimensions in mm

PL/4/H/Z