



More information on the website
mirror.radwag.com/us/info,w1,BSB

LS2208 Barcode Scanner

WX-006-0005



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Construction	
Protection class	IP 30
Communication interface	
Communication interface	RS232 or USB
Environmental conditions	
Operating temperature	0 – +50 °C
Storage temperature	-40 – +70 °C
Physical parameters	
Device dimensions W x D x H	153×85×64 mm
Net weight	146 g
Drop resistance [m]:	1,5 m
Operated barcodes:	1D, 2D, Pdf417, Postal, GS1 Databar
Readout technology:	Imager 2D
Required code contrast [%]:	20 %

Metrological parameters

Permissible ambient humidity [%]:

5 % – 95 %, no condensation

Compatible with (Additional Fee)

MA X7.IC.A Moisture Analyzer
HX7 H Multifunctional Scale
HX7.4N H Multifunctional Stainless Steel Ramp Scale
HX7.4C Multifunctional Platform Scale
HX7 HR Multifunctional Scale
XA 5Y.M.A.P Microbalance for pipettes calibration
WPY Multifunctional Scale
MYA 5Y.P Microbalance for pipettes calibration
C32 Multifunctional Scale
HY10.HRP.H High Resolution Scale
MA 5Y Moisture Analyzer
5Y.PM Precision balance
MYA 5Y.F Microbalance for Filters
HX7.4P2 H Multifunctional Stainless Steel Beam Scales
TMX H Stainless steel Multifunctional Scale
WLY Scales for PGC
AS X7 Analytical Balance
PS X7 Balances for PGC
TMX Multifunctional Scale
XA 5Y.M.A Microbalance
PS R2 Precision Balance
WLC X7 Precision balance
HX7.4N H.LD Multifunctional Stainless Steel Ramp Scale
CY10 Scales for PGC
PUE CY10 Weighing Terminal
CY10 Multifunctional Scale
HX7.4P H Multifunctional Stainless Steel Pallet Scales
HY10 Multifunctional Scale
HY10 H Stainless Steel Multifunctional Scale
HY10.HRP High Resolution Scale
C32.PM Precision Balance
PUE 7.1.HRP High Resolution Scale
Automatic Balances for. Pipettes Calibration
HX7 Multifunctional Scale
MA X7.A Moisture Analyzer
HX7.4 H/Z Multifunctional Stainless Steel Platform Scale, pit version
WPY Scales for PGC
XA 5Y.A Analytical Balance
HX7.4 H Multifunctional Stainless Steel Platform Scale
HX7.4P2 Multifunctional Beam Scales
WAY 5Y.KO Manual Mass Comparator
UYA 5Y Ultra-Microbalance
MA 5Y.IC Moisture Analyzer
MA R Moisture Analyzer
AS 5Y Analytical Balance
AK-4 Automatic Mass Comparator
PS 5Y Precision Balance
PS 5Y Balances for PGC
AKM-2 Automatic Mass Comparator
PS R2.H Precision Balance
HY10.H scales for PGC
DWM/HPW Checkweighers
CY10 Precision balance
Analytical Balance for Filters XA 5Y.F
WLY Precision Balance
UMA Automatic Mass Comparator
PS X7 Precision Balance
APP 5Y.KO Manual Mass Comparator
Robotic Mass Comparators
Density measurement
MYA 5Y Microbalance
PS R1 Precision Balance
XA 5Y Analytical Balance
PUE HX7 Weighing Terminal
5Y.PM.KB Manual Mass Comparator
AS R2 PLUS Analytical Balance
PUE C32 Weighing Terminal
PUE 7.1 Weighing Terminal
PUE 5 Weighing Terminal
HRP 5Y.KO Mass Comparator
Automatic Vacuum Mass Comparators
PMV 5Y Moisture Analyzer
XA 5Y.KO Manual Mass Comparator
HRP 5Y.KB Mass Comparator
XA 5Y.M Microbalance
UYA 5Y.KO Manual Mass Comparator
AS R1 PLUS Analytical Balance
UYA 5Y.F Ultra-Microbalance for Filters
H315 H Waterproof Platform Scale
HX7.4P Multifunctional pallet scales
Nano-Comparator NANO.AK-4.500.5Y
XA 5Y.M.A.S Microbalance for stents weighing
Control Scales for Large Loads