



More information on the website  
[mirror.radwag.com/us/info,w1,C10](http://mirror.radwag.com/us/info,w1,C10)

# HRP 500.1.5Y.KO Mass Comparator

WL-414-0026



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
F1 Calibration Range	500 kg
F2 Calibration Range	100 – 500 kg
M1 Calibration Range	20 – 500 kg
M2 Calibration Range	10 – 500 kg
Maximum capacity [Max]	510 kg
Readability [d]	0,1 g
Standard repeatability [Max]	0,4 g
Standard repeatability [5% Max]	0,2 g
Permissible repeatability	0,6 g
Linearity	±10 g
Eccentricity (tested load)	2d / 1 mm
Electric compensation range	0 – 510 kg
Stabilization time	10 s
Adjustment	internal (automatic)

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	1000×800 mm
Self-centering weighing pan dimensions	600×600 mm
Weighing unit dimensions with self-centering weighing pan	1010×800×275 mm
Controlling device dimensions	249×170×72 mm
Comparator packaging dimensions without self-centering weighing pan	1200×1000×440 mm
Comparator packaging dimensions with self-centering weighing pan	1200×1000×485 mm
Net weight	200 kg
Gross weight	269 kg
Recommended load speed	0,3 m/min
Maximum permissible load speed	0,6 m/min
Weighing unit dimensions without self-centering weighing pan	1010×800×182 mm
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Environmental conditions	
Operating temperature	+15 – +30 °C
Operating temperature change rate	±1 °C / 12 h
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 4 h

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

RFID Tags  
 Self-centering pan for HRP KO comparator  
 Additional modules  
 Protective cover for balances  
 Barcode scanners

THBR 2.0 System - Ambient Conditions Monitoring  
 RS 232, RS 485 cables  
 Receipt Printer  
 Stands, wall mounting kits and mounting brackets  
 Fingerprint Reader

## Software (Additional Fee)

• RAD Key [WX-010-0005]

• RMCS System Network Management of Calibration Process [WX-010-0048]

## Device dimensions W x D x H



Type	A1	A2	H
HRP 200.5Y.KO	809	600	162
HRP 500.5Y.KO	809	600	162
HRP 1000.5Y.KO	1011	800	182
HRP 1500.5Y.KO	1250	1000	235
HRP 2000.5Y.KO	1250	1000	235

Dimensions in mm