



More information on the website  
[mirror.radwag.com/it/info,w1,CB1](https://mirror.radwag.com/it/info,w1,CB1)

# Bilancia pesa pallet C315.4P.600.C

WP-239-0003



The drawings, photos and graphics used are for illustrative purposes only.

## Funzioni



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit  
measurement



GLP Procedures



Animal weighing



ALIBI Memory

## Specifiche

| Parametri metrologici                          |         |
|------------------------------------------------|---------|
| Portata massima [Max]                          | 600 kg  |
| Portata minima [Min]                           | 4 kg    |
| Divisione [d]                                  | 200 g   |
| Intervallo di verifica della bilancia [e]      | 200 g   |
| Campo di tara                                  | -600 kg |
| Massima leggibilità per bilance non verificate | 200 g   |
| Classe OIML                                    | III     |

| Parametri fisici               |                                                |
|--------------------------------|------------------------------------------------|
| Display                        | 4,3" LCD (backlit)                             |
| Lunghezza del cavo             | 3 m                                            |
| Dimensione piatto              | 840×1200 mm                                    |
| Device dimensions L x P x A    | 1322×840×85 mm                                 |
| Dimensioni del pacco L x P x A | 1400×900×430 mm                                |
| Mass scala con indicatore      | 43 kg                                          |
| Costruzione                    |                                                |
| Punteggio IP                   | IP 65 construction, IP 67 cell, IP 43 terminal |
| Interfaccia di comunicazione   |                                                |
| Interfaccia                    | RS232                                          |
| Interfacce opzionali           | RS232                                          |
| Parametri elettrici            |                                                |
| Alimentatore                   | 100 – 240 V AC 50/60 Hz and battery            |
| Massimo assorbimento elettrico | 5 W                                            |
| Tempo operativo delle batterie | max 8h                                         |
| Environmental conditions       |                                                |
| Ambiente di lavoro             | -10 – +40 °C                                   |
| Umidità relativa               | 10% – 85% RH no condensation                   |



Additional fee for verification



## Accessori (Additional Fee)

Alimentatore  
Cavo seriale RS 232 (connessione bilance - Stampanti)  
Supporto, set di montaggio a muro e braccetti di montaggio  
Cavo di alimentazione con spina per accendisigari  
Display  
Cavo seriale RS 232, RS 485




Convertitore RS 232 – Ethernet  
AP2-1 Modulo di conversione analogica  
Convertitore RS 232 – USB  
Convertitore RS 232 – RS 485  
Stampanti di ricevuta

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- Editore per sistemi di pesatura 2.1 [WX-010-0173]

- R-LAB [WX-010-0080]

## Device dimensions L x P x A



Warunki transportu i przemieszczania wagi paletowej przy pomocy kółek jezdnych oraz uchwytów.

Transport of the pallet scale using casters and handles.