



More information on the website  
[mirror.radwag.com/en/info,w1,D27](http://mirror.radwag.com/en/info,w1,D27)

# PL/4/3000/H10/Z Platform

WX-009-0078



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                         |
|--------------------------|-------------------------|
| Maximum capacity [Max]   | 3000 kg                 |
| Readability [d]          | 1 kg                    |
| Construction             |                         |
| Protection class         | IP 66 / 69              |
| Construction             | Stainless steel AISI304 |
| Weighing pan material    | Stainless steel AISI304 |
| Physical parameters      |                         |
| Weighing pan dimensions  | 1500×2000 mm            |
| Weighing platform height | 111 mm                  |

p> **Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.



## Accessories (Additional Fee)

PUE 5 Weighing Terminal  
PUE HX7 Weighing Terminal

PUE 7.1 Weighing Terminal  
PUE HY10 Weighing Terminal

# Device dimensions W x D x H



| Platform   | A    | B    | H       |
|------------|------|------|---------|
| PLC/4/C6   | 800  | 800  | 120 ±10 |
| PLC/4/C7   | 1000 | 1000 | 120 ±10 |
| PLC/4/C8   | 1200 | 1200 | 120 ±10 |
| PLC/4/C8/9 | 1200 | 1500 | 120 ±10 |
| PLC/4/C9   | 1500 | 1500 | 120 ±10 |
| PLC/4/C10  | 1500 | 2000 | 120 ±10 |
| PLC/4/C11  | 2000 | 2000 | 120 ±10 |

dimensions in mm

## PLC/4/C



PL/4/H6/Z  
PL/4/H7/Z  
PL/4/H8/Z



PL/4/H8/9/Z  
PL/4/H9/Z  
PL/4/H10/Z



| Platform  | A    | B    | H      |
|-----------|------|------|--------|
| PL/4/H6   | 800  | 800  | 88 ±2  |
| PL/4/H7   | 1000 | 1000 | 88 ±2  |
| PL/4/H8   | 1200 | 1200 | 88 ±2  |
| PL/4/H8/9 | 1200 | 1500 | 88 ±2  |
| PL/4/H9   | 1500 | 1500 | 88 ±2  |
| PL/4/H10  | 1500 | 2000 | 111 ±2 |

dimensions in mm

## PL/4/H



| Platform    | A    | B    | H      |
|-------------|------|------|--------|
| PL/4/H6/Z   | 800  | 800  | 88 ±2  |
| PL/4/H7/Z   | 1000 | 1000 | 88 ±2  |
| PL/4/H8/Z   | 1200 | 1200 | 88 ±2  |
| PL/4/H8/9/Z | 1200 | 1500 | 88 ±2  |
| PL/4/H9/Z   | 1500 | 1500 | 88 ±2  |
| PL/4/H10/Z  | 1500 | 2000 | 111 ±2 |

dimensions in mm

## PL/4/H/Z