



More information on the website  
[mirror.radwag.com/en/info,w1,D48](https://mirror.radwag.com/en/info,w1,D48)

# DWR 1500 H2 Checkweigher

WK-104-2\_\_



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 – 7500 g
Readability [d]	0.5 – 5 g
Tare range	-1500 – -7500 g
Physical parameters	
Display	12" graphic colour touchscreen
Operating pressure	6 – 8 bar
Construction	
Protection class	IP 55, IP 65
Environmental conditions	
Operating temperature	0 – +40 °C
Components and software	
Operating system	Microsoft Windows 11 IoT
Air consumption	1 liter/measurement

## Features of use

Capacity

max 160 pcs/min



## Accessories (Additional Fee)

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

USB adapter

Receipt Printer

USB cable (scale - printer)