



More information on the website
mirror.radwag.com/en/info,w1,D48

DWR 1500 H2 Checkweigher

WK-104-2___



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	300 – 6000 g
Readability [d]	0.2 – 2 g
Verification unit [e]	0.2 – 2 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Operating pressure	6 – 8 bar
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	Stainless steel
Communication interface	
Communication interface	RS232, USB, Ethernet, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions

Operating temperature -10 – +40 °C

Components and software

Operating system Microsoft Windows 11 IoT

Air consumption 1 liter/measurement

Features of use

Capacity 2 x 80 pcs/min

*OIML class for checkweighers used in packaged goods control (PGC) systems.



Accessories (Additional Fee)

Transponder card readers
RS 232 cables (scale - ZEBRA printer)
RS 232, RS 485 cables

USB adapter
Receipt Printer
USB cable (scale - printer)