



More information on the website  
[mirror.radwag.com/it/info,w1,D48](http://mirror.radwag.com/it/info,w1,D48)

# DWR 1500 H2 sistema automatico controllo peso



The drawings, photos and graphics used are for illustrative purposes only.

## Specifiche

<b>Parametri metrologici</b>	
Portata massima [Max]	1500 – 7500 g
Divisione [d]	0,5 – 5 g
Campo di tara	-1500 – -7500 g
<b>Parametri fisici</b>	
Display	12" graphic colour touchscreen
Pressione operativa	6 – 8 bar
<b>Costruzione</b>	
Punteggio IP	IP 55, IP 65
<b>Environmental conditions</b>	
Ambiente di lavoro	0 – +40 °C
Air consumption	1 liter/measurement
<b>Caratteristiche operative</b>	
Capacità del database	max 160 pcs/min



## Accessori

Lettore di tessere transponder

Cavo seriale RS 232 (connessione bilance - Stampanti ZEBRA)

Cavo seriale RS 232, RS 485

USB adapter

Stampanti di ricevuta

cavo USB (connessione bilance - stampanti)