



# DWR 1500 H2 Checkweigher

WK-104-2\_\_\_

More information on the website  
[mirror.radwag.com/us/info,w1,D48](http://mirror.radwag.com/us/info,w1,D48)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	300 – 6000 g
Readability [d]	0,2 – 2 g
Verification unit [e]	0,2 – 2 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Operating pressure	6 – 8 bar
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	Stainless steel
Communication interface	
Communication interface	RS232, USB, Ethernet, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

### Environmental conditions

Operating temperature -10 – +40 °C

### Components and software

Operating system Microsoft Windows 11 IoT

Air consumption 1 liter/measurement

### Features of use

Capacity 2 x 80 pcs/min



## Accessories (Additional Fee)

Transponder card readers  
RS 232 cables (scale - ZEBRA printer)  
RS 232, RS 485 cables

USB adapter  
Receipt Printer  
USB cable (scale - printer)