



More information on the website  
[mirror.radwag.com/en/info,w1,D80](http://mirror.radwag.com/en/info,w1,D80)

# AVK 1000.5Y Automatic Vacuum Mass Comparator equipped with pumps



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
E1 Calibration Range	100 g – 1 kg
E2 Calibration Range	100 g – 1 kg
F1 Calibration Range	100 g – 1 kg
F2 Calibration Range	100 g – 1 kg
Maximum capacity [Max]	1002 g
Readability [d]	0.1 µg
Standard repeatability [5% Max]	0.4 µg
Standard repeatability [Max]	0.5 µg
Permissible repeatability	1 µg
Electric compensation range	-1 g – +2 g
Stabilization time	60 s
Adjustment	external
Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	ø100 mm

Physical parameters	
Vacuum chamber dimensions	965×745×1150 mm
Pressure range	10 <sup>(-6)</sup> mbar
Object diameters	cylindrical ø (22 – 95)×110; spherical ø (40 – 100) mm
Weighing device dimensions	965×745×1700 mm
Controlling device dimensions	249×170×72 mm
Net weight (without table)	250 kg
Net weight (with table)	650 kg
Supplementary weights external	500 g, 800 g, 900 g
Magazine positions	6
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0.1 °C / 12 h
Relative humidity	45% – 60%

**Repeatability in a vacuum** under model ambient conditions for 6 ABBA cycles.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

RFID Tags  
 Additional modules  
 Protective cover for balances  
 Barcode scanners  
 RS 232, RS 485 cables

THBR 2.0 System - Ambient Conditions Monitoring  
 Receipt Printer  
 Fingerprint Reader  
 RS 232, RS 485 cables  
 RS 232 cables (scale - printer)

## Software

• RMCS Lite [WX-010-0164]

• RMCS System Network Management of Calibration Process [WX-010-0048]

## Device dimensions

