



# CY10.6/15.F1.K.M3.PGC Scale











WK-312-1012

More information on the website  
[mirror.radwag.com/en/info,w1,DIT](http://mirror.radwag.com/en/info,w1,DIT)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  IR sensors
-  Animal weighing
-  Statistical Quality Control
-  Packaged Goods Control
-  Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	6 / 15 kg
Minimum load	40 / 100 g
Readability [d]	2 / 5 g
Verification unit [e]	2 / 5 g
Tare range	-15 kg
Stabilization time	2 s
Adjustment	external

Metrological parameters	
OIML Class	III
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	1 m
Weighing pan dimensions	300×300 mm
Packaging dimensions W x D x H	500×390×410 mm
Net weight	6.3 kg
Gross weight	7.1 kg
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max; 10–19W*
Environmental conditions	
Operating temperature	-10 – +40 °C
Storage temperature	-25 – +70 °C
Multiple range	YES
Features of use	
Max number of platforms	max.2

**Stabilization time** depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



## Accessories (Additional Fee)

### MediaBox

Mild steel powder coated weighing platforms

RFID Tags

Power Adapters

Additional Weighing platforms Module

Additional modules

Platforms in plastic casing

Protective cover for balances

### Barcode scanners

Label Printers

RS 232, RS 485 cables

Stands, wall mounting kits and mounting brackets

Fingerprint Reader

RS 232 – USB Converter

Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions W x D x H

