



More information on the website
mirror.radwag.com/en/info,w1,EMU

PA-04/H Automatic Feeder

WX-001-0105



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Construction | |
|-----------------------------|-------------------------|
| Protection class | IP 34 |
| Communication interface | |
| Communication interface | RS232 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| Power consumption | 95 W |
| Environmental conditions | |
| Operating temperature | +5 – +40 °C |
| Physical parameters | |
| Device dimensions W x D x H | 229×229×303 mm |
| Net weight | 17 kg |
| Gross weight | 26 kg |
| Diameter of fed objects | ø 3 – ø 25 mm |

| | |
|-----------------|------------------------------|
| Feeder diameter | ø 180 mm |
| Throughput | 1 – 15 pcs/min |
| Controlling | external, from balance level |





Compatible with (Additional Fee)

XA 5Y.A Analytical Balance
 Antivibration Tables
 XA 5Y.M.A Microbalance

RS 232, RS 485 cables
 XA 5Y Analytical Balance
 XA 5Y.M Microbalance

Device dimensions W x D x H



[PA-04/H Automatic Feeder](#)