



More information on the website  
[mirror.radwag.com/en/info,w1,EMU](http://mirror.radwag.com/en/info,w1,EMU)

# PA-04/H Automatic Feeder



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Construction             |                         |
|--------------------------|-------------------------|
| Protection class         | IP 34                   |
| Communication interface  |                         |
| Communication interface  | RS232                   |
| Electrical parameters    |                         |
| Power supply             | 100 – 240 V AC 50/60 Hz |
| Power consumption        | 95 W                    |
| Environmental conditions |                         |
| Operating temperature    | +5 – +40 °C             |
| Physical parameters      |                         |
| Device dimensions        | 229×229×303 mm          |
| Net weight               | 17 kg                   |
| Gross weight             | 26 kg                   |
| Diameter of fed objects  | ø 3 – ø 25 mm           |

|                 |                              |
|-----------------|------------------------------|
| Feeder diameter | ø 180 mm                     |
| Throughput      | 1 – 15 pcs/min               |
| Controlling     | external, from balance level |




## Compatible with

XA 5Y.A Analytical Balance  
 Antivibration Tables  
 XA 5Y.M.A Microbalance

RS 232, RS 485 cables  
 XA 5Y Analytical Balance  
 XA 5Y.M Microbalance

## Device dimensions



[PA-04/H Automatic Feeder](#)