



PA-04/H Automatic Feeder

More information on the website
mirror.radwag.com/en/info,w1,EMU



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Construction	
Protection class	IP 34
Communication interface	
Communication interface	RS232
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption	95 W
Environmental conditions	
Operating temperature	+5 ÷ +40 °C
Physical parameters	
Device dimensions	229×229×303 mm
Net weight	17 kg
Gross weight	26 kg
Diameter of fed objects	Ø3 ÷ Ø25 mm

Feeder diameter

ø180 mm

Throughput

1 ÷ 15 pcs/min

Controlling

external, from balance level



Compatible with

XA 5Y.A Analytical Balance

Antivibration Tables


XA 5Y.M.A Microbalance

RS 232, RS 485 cables

XA 5Y Analytical Balance

XA 5Y.M Microbalance

Device dimensions



PA-04/H Automatic Feeder