



More information on the website
mirror.radwag.com/it/info,w1,EQD

DWR 1500 H1 sistema automatico controllo peso

WK-104-1__



The drawings, photos and graphics used are for illustrative purposes only.

Specifiche

Parametri metrologici	
Portata massima [Max]	1500 – 7500 g
Divisione [d]	0,5 – 5 g
Campo di tara	-1500 – -7500 g
Parametri fisici	
Display	12" graphic colour touchscreen
Pressione operativa	6 – 8 bar
Costruzione	
Punteggio IP	IP 55, IP 65
Environmental conditions	
Ambiente di lavoro	0 – +40 °C
Components and software	
Sistema operativo	Microsoft Windows 11 IoT
Air consumption	1 liter/measurement

Caratteristiche operative

Capacità del database

max 80 pcs/min



Accessori (Additional Fee)

Lettore di tessere transponder

Cavo seriale RS 232 (connessione bilance - Stampanti ZEBRA)

Cavo seriale RS 232, RS 485

USB adapter

Stampanti di ricevuta

Cavo USB (connessione bilance - stampanti)