



More information on the website
mirror.radwag.com/us/info,w1,EQD

DWR 1500 H1 Checkweigher

WK-104-1___



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	1500 – 7500 g
Readability [d]	0,5 – 5 g
Tare range	-1500 – -7500 g
Physical parameters	
Display	12" graphic colour touchscreen
Operating pressure	6 – 8 bar
Construction	
Protection class	IP 55, IP 65
Operating temperature	0 – +40 °C
Air consumption	1 liter/measurement
Features of use	
Capacity	max 80 pcs/min



Accessories (Additional Fee)

Transponder card readers
RS 232 cables (scale - ZEBRA printer)
RS 232, RS 485 cables

USB adapter
Receipt Printer
USB cable (scale - printer)