



More information on the website
mirror.radwag.com/us/info,w1,ERT

MA 200/1.5Y.IC.WH Moisture Analyzer

WL-304-0054



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Statistics



IR sensors



GLP Procedures



Replaceable unit



Statistical Quality Control



ALIBI Memory



Drying modes



Samples drying



Moisture content
analysis



Dry mass determination



Wi-Fi

Datasheet

Maximum capacity [Max]	200 g
Readability [d]	0,1 mg
Verification unit [e]	1 mg
Tare range	-200 g
Adjustment	internal (automatic)
OIML Class	I
Maximum sample weight	200 g
Heating module	halogen

Moisture content repeatability	±0,05 % (sample ~ 2 g), ±0,01 % (sample ~ 10 g)
Moisture content readability	0,0001 %
Drying temperature range	Max 250 °C
Physical parameters	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Delivery components	Moisture Analyzer, disposable pan x 10, cross-shaped holder, drying pan handle, weighing pan shield, fabric dust cover, power cord
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions W x D x H	540x610x470 mm
Net weight	5,3 kg
Gross weight	6,8 kg
Construction	
Protection class	IP 43
Features of use	
Display mode	%D, %M, %R, g
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
Communication interface	2xUSB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz
Power consumption	6 W
Heating module power	450 W
Operating temperature	+10 – +40 °C
Mass indication control	External mass standard 50g, 100g, 200g, depending on the type of moisture analyzer (additional equipment)
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)
Drying temperature control	One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set (additional equipment)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

Antivibration tables
Moisture analyzer accessories

Fingerprint Reader
RS 232, RS 485 cables

Additional modules
Barcode scanners
Receipt Printer

RS 232 cables (scale - printer)
RS 232 – RS 485 Converter

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

