



High Resolution Platforms PL.10.HRP.H

WX-009-1174

More information on the website
mirror.radwag.com/en/info,w1,EVL



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|-------------------------|-------------------------|
| Maximum capacity [Max] | 10 kg |
| Minimum load | 5 g |
| Preload range | 4 kg |
| Readability [d] | 0.02 g |
| Tare range | -10 kg |
| Repeatability | 0.03 g |
| Linearity | ±0.06 g |
| Stabilization time | 2 s |
| Adjustment | internal (automatic) |
| Construction | |
| Protection class | IP 66 / 67 |
| Construction | Stainless steel AISI304 |
| Weighing pan material | Stainless steel AISI304 |

| Communication interface | |
|--------------------------------|-------------------------|
| Communication interface | RS232, RS485, Ethernet |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| Environmental conditions | |
| Operating temperature | +10 – +40 °C |
| Relative humidity | 15% – 80% |
| Physical parameters | |
| Weighing pan dimensions | 360×280 mm |
| Device dimensions W x D x H | 360×313×170 mm |
| Packaging dimensions W x D x H | 475×560×370 mm |
| Net weight | 18.7 kg |



Accessories (Additional Fee)

Ethernet cables (scale - Ethernet)
 Antivibration Tables
 PUE 7.1 Weighing Terminal
 RS 232, RS 485 cables
 IN/OUT Cables





Powerbanks
 PUE HY10 Weighing Terminal
 Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
 Weighing Terminal
 RS 232 – USB Converter

Software (Additional Fee)

- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

Device dimensions W x D x H



PL.16 - 32.HRP.H

PL.62-2000.HRP.H

| Scale type | A1 | A2 | H |
|-----------------------|------|------|-------|
| PL.(16-32).HRP.H | 360 | 280 | 180±5 |
| PL.(62-150).HRP.H | 500 | 400 | 180±5 |
| PL.150.2.HRP.H | 500 | 500 | 180±5 |
| PL.(150.1-300).HRP.H | 800 | 600 | 180±5 |
| PL.(300.1-1100).HRP.H | 1000 | 800 | 180±5 |
| PL.(2000).HRP.H | 1250 | 1000 | 180±5 |

Dimensions in mm