



More information on the website
mirror.radwag.com/us/info,w1,F3R

MPS.T.640.R1 Weighing Module

WX-016-0347



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	640 g
Preload range	64 g
Readability [d]	0,01 g
Repeatability	0,01 g
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	external
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	Stainless steel
Communication interface	RS232, max 115,2 kbps, Radwag ASCII protocol
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC

Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
Physical parameters	
Weighing pan dimensions	ø23 mm
Device dimensions W x D x H	220x25x75 mm
Net weight	0,5 kg



Accessories (Additional Fee)

RS 232, RS 485 cables
Antivibration tables

R Terminal (WDM-8)

Software (Additional Fee)

• R Panel [WX-010-0187]

Device dimensions W x D x H

