



More information on the website
mirror.radwag.com/en/info,w1,FDH

DWM HPX Checkweigher

WK-105-0___



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|-------------------------|------------------------------------|
| Maximum capacity [Max] | 1500 – 6000 g |
| Readability [d] | 1 – 2 g |
| OIML Class | XIII (1), Y (a) |
| Physical parameters | |
| Display | 12" graphic colour touchscreen |
| Construction | |
| Protection class | IP 69 K |
| Construction | Stainless steel AISI304 or AISI316 |
| Communication interface | |
| Communication interface | RS232, USB, Ethernet, IN, OUT |
| Components and software | |
| Operating system | Microsoft Windows 11 IoT |

Features of use

Conveyor velocity

1.6 m/s



Accessories (Additional Fee)

Receipt Printer

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]