



More information on the website
mirror.radwag.com/en/info,w1,FDH

DWM HPX Checkweigher

WK-105-002_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 – 7500 g
Readability [d]	1 – 5 g
Verification unit [e]	0.1 – 5 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 69 K
Keypad	touch screen
Construction	Stainless steel
Communication interface	
Communication interface	RS232, USB, Ethernet, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions	
Operating temperature	+5 – +40 °C
Components and software	
Operating system	Microsoft Windows 11 IoT
Features of use	
Capacity	max 500 pcs/min
Conveyor velocity	1.6 m/s

*OIML class for checkweighers used in packaged goods control (PGC) systems.



Accessories (Additional Fee)

Receipt Printer

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]