



More information on the website
mirror.radwag.com/us/info,w1,FDH

DWM HPX Checkweigher

WK-105-0__



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	1500 – 6000 g
Readability [d]	1 – 2 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 69 K
Construction	Stainless steel AISI304 or AISI316
Communication interface	RS232, USB, Ethernet, IN, OUT
Features of use	
Conveyor velocity	1,6 m/s



Accessories (Additional Fee)

Receipt Printer

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]