



More information on the website
mirror.radwag.com/en/info,w1,FNN

DWT/RC HYF Checkweigher

WK-106-001_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	15 – 60 kg
Readability [d]	10 – 20 g
Verification unit [e]	10 – 20 g
OIML Class	XIII (1)*, Y (a)
Physical parameters	
Display	10.1" graphic colour touchscreen
Construction	
Protection class	IP 69 K
Keypad	touch screen
Construction	Stainless steel
Communication interface	
Communication interface	RS232, RS485, Ethernet, USB, IN/OUT
Optional interfaces	Profibus, Profinet, EtherNet/IP, Modbus

Environmental conditions	
Operating temperature	-10 – +40 °C
Components and software	
Operating system	Linux
Features of use	
Capacity	max 50 pcs/min
Conveyor velocity	0.1 – 1 m/s

*OIML class for checkweighers used in packaged goods control (PGC) systems.



Additional fee for verification

Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Receipt Printer

USB cable (scale - printer)