



More information on the website  
[mirror.radwag.com/us/info,w1,FUT](http://mirror.radwag.com/us/info,w1,FUT)

# HX5.EX-1.4N.600.H2 Stainless Steel Ramp Scale

WW-009-0032



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit  
measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

| Maximum capacity [Max] | 600 kg            |
|------------------------|-------------------|
| Minimum load           | 4 kg              |
| Readability [d]        | 200 g             |
| Tare range             | -600 kg           |
| OIML Class             | III               |
| Physical parameters    |                   |
| Display                | 5" graphic colour |

| Physical parameters         |                                                     |
|-----------------------------|-----------------------------------------------------|
| Cable length                | 3 m                                                 |
| Weighing pan dimensions     | 1100×1200 mm                                        |
| Device dimensions W x D x H | 2050×1420×76 mm                                     |
| Net weight                  | 107,8 kg                                            |
| Gross weight                | 108 kg                                              |
| Construction                |                                                     |
| Protection class            | IP 66 / 69 construction, IP 66 / 68 terminal        |
| ATEX Certification          | II 2G Ex ib IIC T4 Gb<br>II 2D Ex ib IIIC T135°C Db |
| IECEX Certification         | Ex ib IIC T4 Gb<br>Ex ib IIIC T135°C Db             |
| Construction                | Stainless steel AISI304                             |
|                             |                                                     |
| Communication interface     | 2×RS232, RS485                                      |
|                             |                                                     |
| Power supply                | 100 – 240 V AC 50/60 Hz                             |
| Power consumption max.      | 15 W                                                |
|                             |                                                     |
| Operating temperature       | -10 – +40 °C                                        |
| Relative humidity           | 10% – 85% RH no condensation                        |
| Indicator                   | PUE HX5.EX-1                                        |



Additional fee for verification



## Accessories (Additional Fee)

Communication modules

Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX

Weighing Terminal

Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]