



PUE 7.1P (panel) Weighing Terminal

WX-008-0026

More information on the website
mirror.radwag.com/en/info,w1,GDY



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Physical parameters	
Display	5.7" resistive colour touchscreen
Device dimensions	215×156×120 mm
Packaging dimensions	300×250×130 mm
Net weight	0.8 kg
Gross weight	2.75 kg
Construction	
Protection class	front IP 66/67, construction IP 32
Keypad	touch screen
Housing	Stainless steel
Communication interface	
Communication interface	2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital)
Additional DP6 A/C converter module	1 (option)
Metrological parameters	
Minimum load cell impedance	50 Ω

Metrological parameters	
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V DC
Maximum increase of signal	19.5 mV
Environmental conditions	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation
Number of buttons	8
Components and software	
Operating system	Linux
Processor	quad-core 64-bit Cortex-A53 1.2 GHz
Memory	RAM 1GB LPDDR2
Data memory	16 GB (micro SD)
Features of use	
Max number of platforms	2



Compatible with (Additional Fee)

Displays

Transponder card readers
 Power Adapters
 RS 232 cables (scale - printer)
 Barcode scanners
 RS 232, RS 485 cables
 Label Printers

IN/OUT Cables

Keypad, external switches
 RS 232, RS 485 cables
 Additional Weighing platforms Module
 RS 232 – USB Converter
 RS 232 cables (scale - printer)
 Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- E2R PGC [WX-010-0051]
- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- E2R Formulations [WX-010-0043]
- E2R Weighing Records [WX-010-0038]
- Audit Trail Reader [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions

