



# PUE 7.1P (panel) Weighing Terminal

WX-008-0026

More information on the website  
[mirror.radwag.com/en/info,w1,GDY](http://mirror.radwag.com/en/info,w1,GDY)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

### Physical parameters

Display	5.7" resistive colour touchscreen
Device dimensions W x D x H	215x156x120 mm
Packaging dimensions W x D x H	300x250x130 mm
Net weight	0.8 kg
Gross weight	2.75 kg

### Construction

Protection class	front IP 66/67, construction IP 32
Keypad	touch screen
Housing	Stainless steel

### Communication interface

Communication interface	2xRS232, 2xUSB-A, Ethernet, 4 IN / 4 OUT (digital)
Additional DP6 A/C converter module	1 (option)

### Metrological parameters

Minimum load cell impedance	50 Ω
-----------------------------	------

<b>Metrological parameters</b>	
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V DC
Maximum increase of signal	19.5 mV
<b>Environmental conditions</b>	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation
Number of buttons	8
<b>Components and software</b>	
Operating system	Linux
Processor	quad-core 64-bit Cortex-A53 1.2 GHz
Memory	RAM 1GB LPDDR2
Data memory	16 GB (micro SD)
<b>Features of use</b>	
Max number of platforms	2



## Compatible with (Additional Fee)

### Displays

Transponder card readers  
 Power Adapters  
 RS 232 cables (scale - printer)  
 Barcode scanners  
 RS 232, RS 485 cables

### Label Printers

IN/OUT Cables  
 Keypad, external switches  
 Additional Weighing platforms Module  
 RS 232 – USB Converter  
 Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Audit Trail Reader [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

## Device dimensions W x D x H

