



PUE 7.1P (panel) Weighing Terminal

WX-008-0026

More information on the website
mirror.radwag.com/us/info,w1,GDY



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Physical parameters | |
|-------------------------------------|--|
| Display | 5,7" Resistive Color Touchscreen |
| Device dimensions W x D x H | 215×156×120 mm |
| Packaging dimensions W x D x H | 300×250×130 mm |
| Net weight | 0,8 kg |
| Gross weight | 2,75 kg |
| Construction | |
| Protection class | front IP 66/67, construction IP 32 |
| Keypad | touch screen |
| Housing | Stainless steel |
| Communication interface | |
| Communication interface | 2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital) |
| Additional DP6 A/C converter module | 1 (option) |
| Electrical parameters | |
| Minimum load cell impedance | 50 Ω |
| Maximum load cell impedance | 1200 Ω |

| | |
|------------------------------|-------------------------------------|
| Load cell excitation voltage | 5V DC |
| Maximum increase of signal | 19,5 mV |
| Operating temperature | -10 – +40 °C |
| Relative humidity | 10% – 85% RH no condensation |
| Number of buttons | 8 |
| Operating system | Linux |
| Processor | quad-core 64-bit Cortex-A53 1,2 GHz |
| Memory | RAM 1GB LPDDR2 |
| Data memory | 16 GB (micro SD) |
| Features of use | |
| Max number of platforms | 2 |



Compatible with (Additional Fee)

Displays

Transponder card readers
Power Adapters
RS 232 cables (scale - printer)
Barcode scanners
RS 232, RS 485 cables

Label Printers

IN/OUT Cables
Keypad, external switches
Additional Weighing platforms Module
RS 232 – USB Converter
Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Audit Trail Reader [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions W x D x H

