



More information on the website
mirror.radwag.com/us/info,w1,GIM

RMC 1000.5Y Robotic Mass Comparator



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E0	10 g – 1 kg *
E1	10 g – 1 kg
E2	10 g – 1 kg
F1	10 g – 1 kg
F2	10 g – 1 kg
Maximum capacity [Max]	1020 g
Readability [d]	1 µg
Standard repeatability [5% Max]	3 µg
Standard repeatability [Max]	4 µg
Permissible repeatability	6 µg
Electric compensation range	-10 g – +20 g
Stabilization time	30 s
Adjustment	external (automatic)
Physical parameters	
Display	10" graphic colour touchscreen

Physical parameters	
Weighing pan dimensions	100×45 mm
Device dimensions	1571×1013×1615 mm
Controlling device dimensions	249×170×72 mm
Magazine positions	40
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	110 – 240 V AC 50/60 Hz
Power consumption max.	200 W
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0,5 °C / 12 h (±0,3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (2% / 4 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

RFID Tags
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables

THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]

Device dimensions

