



More information on the website  
[mirror.radwag.com/en/info,w1,GJ8](https://mirror.radwag.com/en/info,w1,GJ8)

## PL/60/H5 Platform



The drawings, photos and graphics used are for illustrative purposes only.


### Datasheet

| Metrological parameters |                         |
|-------------------------|-------------------------|
| Maximum capacity [Max]  | 60 kg                   |
| Readability [d]         | 20 g                    |
| Construction            |                         |
| Protection class        | IP 68                   |
| Construction            | Stainless steel AISI304 |
| Weighing pan material   | Stainless steel AISI304 |
| Physical parameters     |                         |
| Weighing pan dimensions | 600×600 mm              |
| Packaging dimensions    | 710×710×330 mm          |




### Accessories


## Device dimensions





PL/D2



PLC/F1



PLC/C2  
PLC/C3



PL/H  
PL/HR

| Platform type      | A1  | A2  | H     |
|--------------------|-----|-----|-------|
| PL/D2              | 238 | 216 | 82±3  |
| PLC/F1             | 300 | 300 | 70±3  |
| PLC/C2             | 402 | 502 | 103±3 |
| PLC/C3             | 701 | 501 | 130±5 |
| PL/H1 / PL/HR1     | 150 | 200 | 85±3  |
| PL/H2 / PL/HR2     | 250 | 300 | 103±3 |
| PL/H3 / PL/HR3     | 410 | 410 | 98±3  |
| PL/H3/5 / PL/HR3/5 | 400 | 600 | 155±3 |
| PL/H4 / PL/HR4     | 500 | 500 | 155±3 |
| PL/H5 / PL/HR5     | 600 | 600 | 155±3 |
| PL/H6              | 800 | 800 | 135±3 |

dimensions in mm