



More information on the website  
[mirror.radwag.com/it/info,w1,GOA](https://mirror.radwag.com/it/info,w1,GOA)

# THBR Box Ambient Conditions Recorder

WX-016-0163



The drawings, photos and graphics used are for illustrative purposes only.

## Caratteristiche generali

THBR BOX is an autonomous measuring device operating in a local computer network. THBR Box enables collecting ambient conditions measurements, storing the database, sending customized warnings and alerts and generating website for accessing measurements and settings.

THBR Box There are three models of the recorder: with an integral screen, with a separate screen, without a screen.

Communication with THBR BOX can be established wireless or via Ethernet. The module enables direct connection with up to 4 sensors. With use of USB hub it is possible to connect greater number of sensors. Each sensor has its own identification number that is assigned to measurements saved to the database. THBR Box features the following connectors: 4xUSB, HDMI, Ethernet. The device is powered using external micro USB 5V 2A power supply. Data stored by the THBR Box can be presented via THBR Multi software, website or Android application.



## Compatibile con (Additional Fee)

AS X7 Bilancia analitica  
Bilancia di precisione PS X7  
WAY 5Y.KO Comparatore di massa manuale  
Comparatori di massa robotici  
Bilancia analitica AS 5Y  
Comparatore di massa automatico AK-4  
Bilancia di precisione PS 5Y  
Bilance PS 5Y per controllo CPC  
Comparatore di massa automatico AKM-2  
Comparatore di massa automatico UMA  
APP 5Y.KO Comparatore di massa manuale

Comparatori di densità  
Susceptometri manuali per la misurazione del magnetismo  
5Y.PM.KB Comparatore di massa manuale  
HRP 5Y.KO Comparatore di massa manuale  
Comparatori di massa automatici a vuoto  
Susceptometri automatici per la misurazione del magnetismo  
XA 5Y.KO Comparatore di massa manuale  
HRP 5Y.KB Comparatore di massa manuale  
THBR 2.0 - modulo misura parametri ambientali  
UYA 5Y.KO Comparatore di massa manuale  
Nano-Comparatore NANO.AK-4.500.5Y