



More information on the website
mirror.radwag.com/ja/info,w1,H20

UMA 10.5Y

WL-415-0008



The drawings, photos and graphics used are for illustrative purposes only.

仕様

仕様	
E1 仕様	1 mg – 10 g
E2 仕様	1 mg – 10 g
F1 仕様	1 mg – 10 g
F2 仕様	1 mg – 10 g
最大値 [Max]	10 g
分度値 [d]	0,0001 mg
最大値 [5% Max]	0,2 µg
最大値 [Max]	0,4 µg
分度値	0,6 µg
分度値	0 µg
分度値	0 – 6,1 g
分度値	30 s
分度値	分度値 (分度値)
仕様	
分度値	10" 分度値 + 分度値 分度値

<div style="background-color: #cccccc; padding: 2px;"> Dimensions </div>	
Ø	ø20 mm
Height	950×590×540 mm
Width	460×250×195 mm
Depth	1200×800×1281 mm
Weight	102,5 kg
Net weight	183,5 kg
Capacity	-
Capacity	-
Capacity	36
<div style="background-color: #cccccc; padding: 2px;"> Connectivity </div>	
Ports	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<div style="background-color: #cccccc; padding: 2px;"> Power </div>	
Voltage	100 – 240 V AC 50/60 Hz
<div style="background-color: #cccccc; padding: 2px;"> Environment </div>	
Temperature	+15 – +30 °C
Humidity	±0,5 °C / 12 h (±0,3 °C / 4 h)
Humidity	40% – 60%
Humidity	±5% / 12 h (3% / 4 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional Fee

RFID

RFID

RFID

RFID

RFID

RS 232/RS 485

THBR 2.0 - -

THBR 2.0

THBR 2.0

RS 232/RS 485

RS 232 (-)


Additional Fee

• [WX-010-0005]


• [WX-010-0048]

• [WX-010-0164]


Additional Fee



UMA-100, UMA-1000



UMA-control unit



UMA-5

