



More information on the website
mirror.radwag.com/us/info,w1,H32

MW-01-A6 Mass Converter



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

OIML Class	II or III
Maximum quantity of verification units	10000 e
Minimum volatge per verification unit	0,5 μ V
Maximum voltage per verification unit	1,95 μ V
Minimum load cell impedance	50 Ω
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V DC
Maximum increase of signal	19,5 mV
Connection of load cells	4 or 6 wires + shield
Construction	
Protection class	IP 66
Housing	aluminum
Communication interface	RS232, ETHERNET IP, 3xIN / 3xOUT
Power supply	100 – 240 V AC 50/60 Hz

Operating temperature	-10 – +40 °C
Physical parameters	
Packaging dimensions	300×250×130 mm
Net weight	1 kg
Gross weight	1,4 kg
Multiple range	YES
Features of use	
Max number of platforms	1

Compatible with

RS 232 – USB Converter

Displays

Software

- RAD Key [WX-010-0005]
- RADWAG Development Studio [WX-010-0104]

- MW Manager [WX-010-0113]

Device dimensions

