



More information on the website  
[mirror.radwag.com/en/info,w1,HA6](http://mirror.radwag.com/en/info,w1,HA6)

# C315.4P.1500/3000.C Pallet Scale

WP-239-1000



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

- Plus/Minus Control
- Percent Weighing
- Totalizing
- Parts counting
- Internal battery
- Peak hold
- Newton unit measurement
- GLP Procedures
- Animal weighing
- ALIBI Memory

## Datasheet

| Metrological parameters |                |
|-------------------------|----------------|
| Maximum capacity [Max]  | 1500 / 3000 kg |
| Minimum load            | 10 kg          |
| Readability [d]         | 0.5 / 1 kg     |
| Verification unit [e]   | 0.5 / 1 kg     |
| Tare range              | -3000 kg       |
| OIML Class              | III            |

| Physical parameters            |  |
|--------------------------------|--|
| Display                        | 4.3" LCD (backlit)                             |
| Cable length                   | 3 m  |
| Weighing pan dimensions        | 840×1200 mm                                    |
| Device dimensions W x D x H    | 1322×840×85 mm                                 |
| Packaging dimensions W x D x H | 1400×900×430 mm                                |
| Scale mass with indicator      | 43 kg  |
| Construction                   |  |
| Protection class               | IP 65 construction, IP 67 cell, IP 43 terminal |
| Communication interface        |  |
| Communication interface        | RS232  |
| Optional interfaces            | RS232  |
| Electrical parameters          |  |
| Power supply                   | 100 – 240 V AC 50/60 Hz and battery            |
| Power consumption max.         | 5 W  |
| Operation time on batteries    | max 8h   |
| Environmental conditions       |  |
| Operating temperature          | -10 – +40 °C                                   |
| Relative humidity              | 10% – 85% RH no condensation                   |



Additional fee for verification



## Accessories (Additional Fee)

Power Adapters  
 RS 232 cables (scale - printer)  
 Stands, wall mounting kits and mounting brackets  
 Cigarette lighter receptacle power supply cables  
 Displays  
 RS 232, RS 485 cables



RS 232 – Ethernet Converter  
 AP2-1 Current Loop Unit  
 RS 232 – USB Converter  
 RS 232 – RS 485 Converter  
 Receipt Printer

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- Scale Editor 2.1 [WX-010-0173]

- R-Lab [WX-010-0080]

## Device dimensions W x D x H



Warunki transportu i przemieszczania wagi paletowej przy pomocy kółek jezdnych oraz uchwytów.

Transport of the pallet scale using casters and handles.