



More information on the website
mirror.radwag.com/en/info,w1,HA6

C315.4P.1500/3000.C Pallet Scale

WP-239-1000



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Plus/Minus Control
-  Percent Weighing
-  Totalizing
-  Parts counting
-  Internal battery
-  Peak hold
-  Newton unit measurement
-  GLP Procedures
-  Animal weighing
-  ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 / 3000 kg
Minimum load	10 kg
Readability [d]	500 / 1000 g
Verification unit [e]	500 / 1000 g
Tare range	-3000 kg
OIML Class	III

Physical parameters		
Display		4.3" LCD (backlit)
Cable length		3 m
Weighing pan dimensions		840×1200 mm
Device dimensions W x D x H		1322×840×85 mm
Packaging dimensions W x D x H		1400×900×430 mm
Scale mass with indicator		43 kg
Construction		
Protection class		IP 65 construction, IP 67 cell, IP 43 terminal
Communication interface		
Communication interface		RS232
Optional interfaces		RS232
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz and battery
Power consumption max.		5 W
Operation time on batteries		max 8h
Environmental conditions		
Operating temperature		-10 – +40 °C
Relative humidity		10% – 85% RH no condensation



Additional fee for verification



Accessories (Additional Fee)

Power Adapters
 RS 232 cables (scale - printer)
 Stands, wall mounting kits and mounting brackets
 Cigarette lighter receptacle power supply cables
 Displays
 RS 232, RS 485 cables




RS 232 – Ethernet Converter
 AP2-1 Current Loop Unit
 RS 232 – USB Converter
 RS 232 – RS 485 Converter
 Receipt Printer

Software (Additional Fee)

• RAD Key [WX-010-0005]
 • Scale Editor 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

Device dimensions W x D x H



Warunki transportu i przemieszczania wagi paletowej przy pomocy kółek jezdnych oraz uchwytów.

Transport of the pallet scale using casters and handles.